

Search Results

Evaluate

- Advertisements
- PDF-J-pro Cable ..
- FAQ's

Design a Solution

- Part Drawings
- PDF-J-Pro Cable ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'JP2CM-L2'

Your search criteria matched only one product, shown below

JP2CM-L2



- Complete horizontal and vertical 1" bend radius control helps prevent degradation of cable performance
- UL 2043 and CAN/ULC S102.2 approved and are suitable for use in air handling spaces
- Durable non-metallic J Hook materials provide the ability to manage and support a large number of cables
- Pre-riveted assemblies allow for attachment to ceilings, beams, threaded rods, drop wires and under floor supports to meet requirements of a variety of applications
- Wide cable support base prevents pinch points that could cause damage to cables
- Cable tie channel allows user to easily install 3/4" *Tak-Ty*[®] Cable Ties to retain cable bundle

| | |
|------------------------------|---|
| Part Number | JP2CML2 |
| RoHS Compliancy Status | RoHS directive is not applicable |
| Part Description | J Hook with ceiling mount bracket that has one 3/16" (M5), 1/4" (M6), and 3/8" (M10) mounting hole. |
| Material | Nylon 6.6 J Hook with metal attachments |
| Color | Red |
| 10Gig (.33") | 28 |
| CAT 5E (.193") | 56 |
| CAT 6 (.248") | 31 |
| CAT 6Plus (.26") | 23 |
| Max. Bundle Diameter (In.) | 2.00 |
| Max. Bundle Diameter (mm) | 50.8 |
| Max. Static Load (Kg) | 13.6 |
| Max. Static Load (Lbs.) | 30 |
| Pricing Description | J-Pro Cable Support System Ceiling Mount, Red |
| Min. Order UOM | PC |
| Min. Order Qty. | 50 |
| BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| Add to Favorite Product List |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.