

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'LCDX500-38D-6'


Your search criteria matched only one product, shown below

LCDX500-38D-6



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- American Bureau of Shipping Approved
- Available with NEMA hole sizes and spacing

▪ Part Number	LCDX500-38D-6
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Flex Lug, 500 kcmil, 2hole, 3/8" Stud Holes, 1.00 Hole Spacing
▪ CSA Certified	Yes
▪ UL Listed	Yes
▪ Length (In.)	4.08
▪ Length (mm)	103.6
▪ Class G,H, I, K, M	500 kcmil
▪ Diesel Locomotive	535.3 kcmil
▪ Stud Hole Size (In.)	3/8
▪ Stud Hole Spacing (In.)	1.00
▪ Tongue Width (In.)	1.89
▪ Barrel Length (In.)	1.48
▪ Angle	Straight
▪ Panduit Color Code	Pink
▪ Panduit Die Index No.	P99
▪ Pricing Description	Copper Comp. Lug, 2 Hole, 500 kcmil Flex, 3/8" (9.5mm) Stud, 1" (25.4mm) Hole Spacing
▪ Stud Hole Size (mm)	M8
▪ Tongue Thickness	.26
▪ Tongue Type	Standard
▪ Tongue Width (mm)	48.0
▪ Wire Strip Length (In.)	1 9/16
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ Burndy Die Index No.	L99
▪ T&B Die Index No.	99H
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.