

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFMetric Ring ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'PM2-4R-X'

Your search criteria matched only one product, shown below

PM2-4R-X



- Ring tongue design assures a secure connection in high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process
- Barrel of terminal internally beveled to provide quick and easy wire insertion
- Maximum recommended operating temperature 302°F (150°C)

Part Number	PM24R-X
RoHS Compliancy Status	Compliant
Part Description	Metric ring terminal, 1.5– 2.5mm ² wire range, M4 stud size, non-insulated.
Product Type	Terminals- Metric
Length (mm)	18.0
Width (mm)	7.9
Clearance	7.4
Pricing Description	Metric Ring Terminal, norinsulated, 1.5 – 2.5mm ² wire range, M4 stud size
Stud Size	M4
Tool	CT-1570, CT-2500
Wire Range (mm ²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	10
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.