

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDFMetric Ring ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'PM6-3R-X'

Your search criteria matched only one product, shown below

## PM6-3R-X



- Ring tongue design assures a secure connection in high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process
- Barrel of terminal internally beveled to provide quick and easy wire insertion
- Maximum recommended operating temperature 302°F (150°C)

|                               |  |
|-------------------------------|--|
| Part Number                   | PM6-3R-X   |
| RoHS Compliancy Status        | Compliant  |
| Part Description              | Metric ring terminal, 2.5– 6.0mm <sup>2</sup> wire range, M3 stud size, non-insulated. |
| Product Type                  | Terminals- Metric  |
| Length (mm)                   | 19.2   |
| Width (mm)                    | 5.8  |
| Clearance                     | 7.9  |
| Pricing Description           | Metric Ring Terminal, norinsulated, 2.5– 6.0mm <sup>2</sup> wire range, M3 stud size   |
| Stud Size                     | M3   |
| Tool                          | CT-1570, CT-2500   |
| Wire Range (mm <sup>2</sup> ) | 2.5 – 6.0  |
| Min. Order UOM                | PC   |
| Min. Order Qty.               | 10   |
| BOM Qty. (# of Pkgs.)         | <input type="text" value="0"/>   |
| Add to Favorite Product List  |   |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.