



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'PV18-14FB-3K'

Your search criteria matched only one product, shown below

PV18-14FB-3K



The PVC insulation forms an insulation crimp on the wire insulation. All polyvinylchloride 2 - piece insulated terminals are rated at 600 volts and designed for up to 105° C (221° F) operating temperature.

- Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time
- Fork design provides for fast and easy installation, without the need to remove fastener
- Insulation support helps to prevent wire damage in bending applications
- Maximum insulation temperature 221°F (105°C)
- UL and CSA rated up 600 V per UL 486

Part Number	PV18-14FB-3K
RoHS Compliancy Status	Compliant
Part Description	Fork Terminal, vinyl insulated, funnel entry, plastic insulation crimp, 22- 18 AWG wire range, 1/4" stud size.
Product Type	Terminals- Reel Fed
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.03
Width (In.)	.44
Barrel to Hole Length (In.)	.78
CA-800 Series Crimp Die	CD-800-1
CA9 Series Crimp Die	CD9-1A
Clearance	.33
Max. Ins.	.150
Panduit Color Code	Red
Pieces Per Reel	3000
Pricing Description	Fork Terminal, vinyl insulated, 22- 18 AWG, 1/4" stud size, funnel entry
Stock	.03
Stud Size	1/4"
Wire Range	22 – 18 AWG
Wire Range (mm ²)	0.5 - 1.5
Min. Order UOM	PC
Min. Order Qty.	3000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.