

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDFGrounding Bu ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'RGRB19'

Your search criteria matched only one product, shown below

## RGRB19Y



- Provides the common grounding point within the cabinet
- Optimized for installation on 19" racks or cabinets that meet EIA -310-D
- Can be positioned anywhere on the rack or cabinet
- Available pre-assembled with twenty mounting screws for quick and easy installation
- Engineered to comply with US and International grounding requirements

Part Number	RGRB19Y
RoHS Compliancy Status	Compliant
Note	RGRB19Y replaces RGRB19
Part Description	Grounding busbar; 19" (483mm) length; tinplated; fourteen holes arranged for flexibility in mounting; provided with two each #12-24 x 1/2" and M6 x 12mm threadforming screws.
CSA Certified	Yes
UL Listed	Yes
Pricing Description	Grounding Busbar Kits, 19" (483mm) Lgth, 14 mounting holes, 1/2" (12.7mm) Hole Spacing
Min. Order UOM	KT
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.