

Products

Products Overview

Product Search

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDF Copper Butt ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Product Search](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results

Part Number > **SCS1-E**


Your search criteria matched only one product, shown below

SCS1-E



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

Part Number	SCS1-E
RoHS Compliancy Status	Compliant
Part Description	Copper Butt Splice, standard barrel, #1 AWG wire.
Product Type	Compression Connectors- Splices
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.87
Length (mm)	47.5
Copper Conductor Size	#1 AWG
Barrel O.D.	.47
Barrel I.D.	.36
Panduit Color Code	Green
Panduit Die Index No.	P37
Pricing Description	Copper Compression Butt Splice, Standard Barrel, #1 AWG
Wire Strip Length (In.)	7/8
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	11
T&B Die Index No.	37
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.