

Current refinements (click to remove)

[Search Tips](#)

Region [USA](#) Product Family [Tie Harness Mounts](#) Text Search: 'THMSP25-M'

Your search criteria matched only one product, shown below.



Tie Harness Mounts are designed to be attached to the wire harness during assembly with 2 cable ties. Ties can be installed by hand or more efficiently with *PANDUIT* Automatic Cable Tie Tooling. Use with Harness Board Standoff Posts. Available with or without corrugated tubing location tab.

Part Number:	THMSP25M
RoHS Compliancy Status:	Compliant
Part Description:	Harness Cable Tie Mount
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Height (In.):	.54
Height (mm):	18.3
Length (In.):	1.54
Length (mm):	39.1
Width (In.):	.37
Width (mm):	9.4
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Panel Thickness (In.):	.230
Max. Panel Thickness (mm):	5.8
Mounting Method:	Push barb
Panel Hole Diameter Range (In.):	.244 – .283
Panel Hole Diameter Range (mm)	6.2 – 7.2
Used With Cable Ties:	M, I, S
Min. Order UOM:	PC
Min. Order Qty.:	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>

Add to My Catalog



Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.