

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results


 **Text Search: 'UTPCH13RDY'**

Your search criteria matched only one product, shown below

UTPCH13RDY



- Exceed TIA/EIA568-B.2 Category 5e and ISO11801 Class D standards
- Each patch cord is 100% performance tested and wired T568A
- Constructed of Category 5e, 24 AWG UTP stranded cable and *Pan-Plug*® Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable TIA -968-A-3 requirements and exceeds IEC 60603 -7 specifications
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Labels on patch cords provide identification of performance level, length, and quality control number
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color coding options
- Optional RJ45 Plug Lock -In Device blocks unauthorized removal of cable, IP phone, other networking equipment or critical connection
- Third party tested to Category 5e component compliance

Part Number	UTPCH13RDY
RoHS Compliancy Status	Compliant
Part Description	Category 5e, UTP patch cord with PanPlug™ Modular Plugs on each end.
Product Type	Copper Patch Cord
Color	Red
Length (ft.)	13
Length (m)	3.96
Boot Color	No Boot
Cable Color	Red
Cable Type	UTP
Flammability Rating	CM
Performance Level	Category 5e
Pricing Description	Copper Patch Cord, Category 5e, Red UTP Cable, 13 Feet
Wiring Scheme	T568A
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.