


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFPK18-4R-C Pr
 - Part Drawings
 - PDFRing Termina..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PK8-14R-T'

Your search criteria matched only one product, shown below

PK8-14R-T



- Designed for use with #8 – 2 AWG copper wire
- For nuclear containment areas and high temperature to 300°F (150°C) applications
- Color coded: Natural with appropriate color stripe to identify wire range
- Ring tongue design assures a secure connection in high vibration applications
- Classified as Class 1E in accordance with IEEE 323 -2003
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications

Part Number	PK8-14R-T
RoHS Compliancy Status	Compliant
Part Description	Ring terminal, #8 AWG, KYNAR insulated, 1/4" stud size.
Color	Red Stripe
UL Listed	Yes
Length (In.)	1.52
Length (mm)	38.6
Width (In.)	0.47
Width (mm)	11.9
Clearance	0.43
Clearance (mm)	10.9
Insulation	Kynar
Max. Ins.	0.326
Max. Ins. (mm)	8.28
Panduit Color Code	Red Stripe
Plating Type	Tinned
Pricing Description	Ring Terminal, large wire, KYNAR insulated, 8 AWG, 1/4" stud size
Stock	0.04
Stock (mm)	1.0
Stud Size	1/4"
Temperature Rating	300 Degrees Fahrenheit (150 Degrees Celsius)
Tool	CT-2600, CD-2600-8†
Wire Range	8 AWG
Wire Range (mm ²)	10mm ²
Min. Order UOM	PC
Min. Order Qty.	200
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.