

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDFPart Drawing ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PLB5EH-C0'

Your search criteria matched only one product, shown below

**PLB5EH-C0**



- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- A fast and economical method to secure and separate two bundles
- Reduces part number inventory – single part covers multiple bundle sizes
- Installs easily by hand – second loop can be installed with Panduit cable tie installation tools

Part Number	PLB5EH-C0
RoHS Compliancy Status	Compliant
Part Description	Double Loop Cable Tie, 19.2", Extra-Heavy cross section
Product Type	Cable Ties
Material	Weather Resistant Nylon 6.6
Color	Black
CSA Certified	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Length (In.)	19.2
Length (mm)	488
Width (In.)	0.500
Width (mm)	12.7
CE Compliant	Yes
Cross Section	Extra-Heavy
Head Height (In.)	0.400
Head Height (mm)	10.2
Head Length (In.)	1.2
Head Length (mm)	30.5
Head Width (In.)	0.800
Head Width (mm)	20.3
Locking Style	Locking
Material Flammability Rating	HB
Max. Combined Bundle Dia. (In.)	5.2
Max. Combined Bundle Dia. (mm)	132
Max. Continuous Use Temperature	185°F (85°C)
Min. Loop Tensile Strength (Lbs.)	125
Min. Loop Tensile Strength (N)	556
Plenum Rated	No
Pricing Description	Double Loop Tie, 19.2"L (488mm), Extra-Heavy, Weather Resistant Nylon, Black
Thickness (In.)	0.075
Thickness (mm)	1.9
Tool	GS4EH, ST3EH
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.