

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF Ring Termina ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PN12-38HDR-2K'


Your search criteria matched only one product, shown below

PN12-38HDR-2K



This 3-piece design terminal provides a permanently attached tin plated brass sleeve for insulation grip in funnel or straight entry sleeve designs. This product feature offers the highest quality reliable terminations. Nylon insulation is rated at 600 volts and designed for up to 105° C (221° F) operating temperature.

- Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time
- Manufactured from stock 56% thicker than a standard #16 – 14 AWG terminal for use in heavy duty applications
- Insulation housing is marked with “HDR” to signify heavy-duty ring
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 486

Part Number	PN1238HDR2K
RoHS Compliancy Status	Compliant
Part Description	Heavy Duty Ring Terminal, nylon insulated, metal insulation grip sleeve, 16 12 AWG wire range, .05 stock and 3/8" stud size.
Product Type	Terminals- Reel Fed
CSA Certified	Yes
UL Listed	Yes
Length (In.)	1.28
Width (In.)	.58
Barrel to Hole Length (In.)	.98
CA-800 Series Crimp Die	CD-800-3
CA9 Series Crimp Die	CD9-3B
CE Compliant	No
CE Marking	No
Clearance	.38
Max. Ins.	.225
Panduit Color Code	Yellow
Pieces Per Reel	2000
Pricing Description	Ring Terminal, heavy duty, nylon insulated, 16 12 AWG, 3/8" stud size
Stock	.05
Stud Size	3/8"
Wire Range	16 – 12 AWG
Wire Range (mm ²)	1.5 – 4.0
Min. Order UOM	PC
Min. Order Qty.	2000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.