

### Search Results

#### Evaluate

- FAQ's
- Line Cards
- PDFCable Access ..

#### Design a Solution

- Part Drawings
- PDFBridle Ring..
- Specification Sheets
- PDFCable Access ..

#### How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

## Home > Products Overview > Search Results >

Current refinements (click  to remove) [Search Tips](#)

 Text Search: 'BR-2.0-1/4-20'

Your search criteria matched only one product, shown below

### BR-2.0-1/4-20



- Multiple diameters, thread sizes, and configurations
- Threaded and non-threaded sizes are compatible with spring steel clip (BR -MPCL) clamp providing a solid securing point for the bridle ring
- Other unique labor saving assemblies differentiate from competition – including pre-assemblies with powder actuated fasteners, toggle wings, and clearance holes for user supplied fasteners

Part Number	BR-2.0-1/4-20
RoHS Compliancy Status	Compliant
Part Description	Bridle ring, 2.00" dia., 1/4– 20 threaded.
Material	Low carbon steel with bright zinc electroplate
Max. Bundle Capacity (In.)	2.00
Max. Bundle Capacity (mm)	51
Overall Height (In.)	3.9
Overall Height (mm)	99
Pricing Description	Bridle Ring, 2.00" Dia., 1/4 20 Threaded
Ring Size	2"
Thread size	1/4"– 20 threaded
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.