


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFRing Termina..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PV22-6R-MY'

Your search criteria matched only one product, shown below

PV22-6R-MY



- Insulation support helps to prevent wire damage in bending applications
- Ring tongue design assures a secure connection in high vibration applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up 600 V per UL 486A/B

‡UL and CSA approved tooling/product combinations.

Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number	PV22-6R-MY
RoHS Compliancy Status	Compliant
Note	PV22-6R-MY replaces PV22-6R-M
Part Description	Ring Terminal, 26– 22 AWG, #6 stud size, vinyl insulated, funnel entry.
Product Type	Terminals
CSA Certified	No
UL Listed	No
Length (In.)	0.68
Length (mm)	17.3
Width (In.)	0.21
Width (mm)	5.3
CE Compliant	No
Clearance	0.18
Clearance (mm)	4.6
Insulation	vinyl
Max. Ins.	0.110
Max. Ins. (mm)	2.8
Panduit Color Code	Yellow
Plating Type	Tinned
Pricing Description	Ring Terminal, vinyl insulated, 26 22 AWG, #6 stud size, funnel entry
Stock	0.02
Stock (mm)	0.5
Stud Size	#6
Tool	CT-100A, CT-600-A, CT-1525, CT-2500
Wire Range	26 – 22 AWG
Wire Range (mm ²)	0.14 – 0.50
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.