

Search Results

Evaluate


- FAQ's
- Selection Guides
- PDF Convenience..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PNF14-10R-E'

Your search criteria matched only one product, shown below

PNF14-10R-E



- Ring tongue design assures a secure connection in high vibration applications
 - Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
 - UL and CSA rated up to 600 V per UL 486A/B
- ‡UL and CSA approved tooling/product combinations.

Part Number	PNF1410R-E
RoHS Compliancy Status	Compliant
Part Description	Ring Terminal, 16- 14 AWG, #10 stud size, funnel entry, nylon insulated.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	0.85
Length (mm)	21.6
Width (In.)	0.31
Width (mm)	7.9
CE Compliant	No
Clearance	0.29
Clearance (mm)	7.4
Insulation	Nylon
Max. Ins.	0.162
Max. Ins. (mm)	4.12
Panduit Color Code	Blue
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Stock	0.03
Stock (mm)	0.8
Stud Size	#10
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1551‡, CT-2500‡
Wire Range	16 – 14 AWG
Wire Range (mm²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.