

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results

 Text Search: 'PPS0710N443'

Your search criteria matched only one product, shown below

PPS0710N443



Indoor / Outdoor SubSurface Printed Adhesive Polyester (Type PPS)

- High quality signs for use indoors and outdoors
- Excellent resistance to UV light, chemical atmosphere, and abrasion
- Excellent life and adhesion properties
- Printed graphics are protected by clear polyester laminate


Indoor/Outdoor Rigid Polyethylene (Type PRS)

- Rugged signs for indoors and outdoors
- Abrasion resistant
- Used where adhesives will not work

• Can be used with *PANDUIT* Thermal Transfer Desktop Printers and *Easy-Mark™* Labeling Software to create your own custom signs

– Print your own legend on clear polyester tape with the TDP43MY Thermal Transfer Desktop Printer and adhere label to adhesive or non-adhesive sign panel

- Can also be used with *PANDUIT* Die Cut Letter and Numbers

• Part Number	PPS0710N443
• RoHS Compliancy Status	Compliant
• Part Description	Adhesive Sign, 7"H x 10"W, 'Notice'
• Material	GMM Polyester
• Height (In.)	7.00
• Height (mm)	177.80
• Width (In.)	10.00
• Width (mm)	254.00
• Color (Legend/Background)	Blue and Black/White
• Legend	(Blank)
• Pricing Description	Adhesive Sign, Polyester, 'Notice (header only)', 10"x7", 1 sgn/cd, 5 cds/pk, BB/WH
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.