


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFPV8-8R-QY Pr
 - Part Drawings
 - PDFRing Termina..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PV8-12R-XY'

Your search criteria matched only one product, shown below

PV8-12R-XY



- Ring tongue design assures a secure connection in high vibration applications
 - Insulation support helps to prevent wire damage in bending applications
 - Brazed seam protects terminal barrel from splitting during the crimp process
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
 - UL rated up to 600 V per UL 486A/B
- ‡UL approved tooling/product combinations.

Part Number	PV8-12R-XY
RoHS Compliancy Status	Compliant
Note	PV8-12R-XY replaces PV8-12R-QY
Part Description	Ring Terminal, large wire, 8 AWG, 1/2" stud size, vinyl insulated.
Product Type	Terminals
UL Listed	Yes
Length (In.)	1.74
Length (mm)	44.2
Width (In.)	0.82
Width (mm)	20.8
CE Compliant	No
Clearance	0.51
Clearance (mm)	13.0
Insulation	Vinyl
Max. Ins.	0.280
Max. Ins. (mm)	7.1
Panduit Color Code	Red
Plating Type	Tinned
Pricing Description	Ring Terminal, large wire, vinyl insulated, 8 AWG, 1/2" stud size
Stock	0.04
Stock (mm)	1.0
Stud Size	1/2"
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-720, CD-720PV8-2‡, CT-2600, CD-2600-PV8‡
Wire Range	8 AWG
Wire Range (mm²)	10
Min. Order UOM	PC
Min. Order Qty.	10
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.