

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFPW38F-TL Pro
 - PDFPW38F-TL Pro
 - Part Drawings
 - PDFPan-Wrap Spl..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PW150FR-L20Y'

Your search criteria matched only one product, shown below


PW150FR-L20Y



- Slot pattern provides improved flexibility and abrasion protection
- Unique wall design allows easy wire or cable breakouts
- Innovative design maintains uniform bundle protection in dynamic applications; large overlap accommodates a wide range of bundle diameters
- Packaged on a reel for convenient handling and dispensing of product
- Patented installation tool with 180° opening allows easy loading of maximum bundle diameters to speed installation

Notes:

- 1) Order number of reels required.
- 2) Diameter can be further reduced with the use of cable ties.
- 3) Flame retardant products are manufactured from a material that is rated UL 94V -0.

Part Number	PW150FRL20Y
RoHS Compliancy Status	Compliant
Note	PW150FRL20Y replaces PW150FRL20
Part Description	1 1/2" Pan-Wrap™ Split Harness Wrap
Product Type	Pan-Wrap
Material	Flame Retardant Polyethylene
Color	Black
CE Compliant	No
Flammability Rating	V-0
Length Per Reel (ft.)	50
Length Per Reel (m)	15.2
Material Flammability Rating	UL 94V-0
Max. Bundle Diameter (In.)	1.63
Max. Bundle Diameter (mm)	41.3
Min. Bundle Diameter (In.)	1.13
Min. Bundle Diameter (mm)	28.6
Nominal Diameter / Size	1 1/2 inch
Nominal I.D. (In.)	1.50
Nominal I.D. (mm)	38.1
Pricing Description	1 .50"(38.1mm) Panwrap, Black Flame Retardant, 50 ft. (15m) per roll
Temperature Range	-4°F– 167°F (-20°C– 75°C)
Tool	PWT150
Type	Pan-Wrap
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.