



Search within category

- Categories**
- Wire Termination
- Power Connectors
- Copper Mechanical Lugs and Splices



CO35-36SL-QY

Two-hole, copper, single barrel, offset floating tongue lug, slotted screw, #14 - #6 AWG, 3/16" (4.8mm) stud hole.

Hex Size (In.)	**
Tongue Width (mm)	9.7
Height (In.)	0.49
Height (mm)	12.4
Length (In.)	2.19
Length (mm)	55.6
Copper Conductor Size Range	#14 AWG - #6 AWG, (2) #10 AWG, (2) #12 AWG, (2) #14 AWG, (1) #10 AWG with (1) #12 AWG, (1) #12 AWG with (1) #14 AWG
Current Rating (Amps)	50
Tongue Thickness (mm)	1.8
Stud Hole Size (In.)	3/16
Tightening Torque (In-Lbs)	20-35
Tongue Width (In.)	0.38
Tongue Thickness	0.07
Hex Size (mm)	**
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000