



Current refinements (click to remove)
[Search Tips](#)
 [Region](#) [USA](#)
 [Product Family](#) [Spiral Wrap](#)
 [Text Search: 'T62F-TL'](#)
Your search criteria matched only one product, shown below.


- Largest variety of colors materials and sizes in the industry
- Available in seven different materials and twelve different colors
- Colors conform to Communications Wiring Standards
- Flexible, neat, fast
- Allows breakouts of single/multiple wires and rerouting of replacement wires
- Harness multiple cables into a single manageable bundle
- A protection for wires cables hoses and tubing
- Color code wire bundles
- Reusable
- Tool supplied in each package

*Order number of reels required.

**Flame retardant products are manufactured from a material that is rated UL94V-0.

‡Reel packaging may contain splices.

Contact Customer Service for availability of additional sizes and materials.

Part Number:	T62F-TL
RoHS Compliance Status:	Compliant
Part Description:	Spiral Wrap offers abrasion protection for wires, cables, hoses and tubing
Material:	Polyethylene
Color:	Natural
UL Recognized:	E141152
Length (ft.):	250
Length (m):	76.2
Bundle Diameter Range (In.):	1/2 to 4 1/2
Bundle Diameter Range (mm):	12.7 to 114.3
Flammability Rating:	UL94 HB
Min. Bundle Diameter (In.):	1/2
Min. Bundle Diameter (mm):	12.7
Outside Diameter (In.):	.62
Outside Diameter (mm):	15.9
Temperature Range:	-40°F to 122°F (-40°C to 50°C)
Wall Thickness (In.):	.06
Wall Thickness (mm):	1.57
Wrap Width (In.):	.63
Wrap Width (mm):	15.9
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.