


[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

 Text Search: 'T25FR-MY'

Your search criteria matched only one product, shown below

T25FR-MY



- Largest variety of colors materials and sizes in the industry
 - Available in seven different materials and twelve different colors
 - Colors conform to Communications Wiring Standards
 - Flexible, neat, fast
 - Allows breakouts of single/multiple wires and rerouting of replacement wires
 - Harness multiple cables into a single manageable bundle
 - A protection for wires cables hoses and tubing
 - Color code wire bundles
 - Reusable
 - Tool supplied in each package
- *Order number of reels required.
- **Flame retardant products are manufactured from a material that is rated UL94V -0.

‡Reel packaging may contain splices.

Contact Customer Service for availability of additional sizes and materials.

Part Number	T25FRMY
RoHS Compliancy Status	Compliant
Note	T25FRMY replaces T25FRM
Part Description	Spiral Wrap offers abrasion protection for wires, cables, hoses and tubing
Product Type	Spiral Wrap
Material	Flame Retardant Polyethylene
Color	Natural
UL Recognized	E141152
Length (ft.)	1,000
Length (m)	304.8
Bundle Diameter Range (In.)	3/16 – 2
Bundle Diameter Range (mm)	4.8 – 50.8
CE Compliant	No
Flammability Rating	V-0
Length Per Reel (ft.)	1,000
Length Per Reel (m)	304.8
Max. Bundle Capacity (In.)	2.0
Max. Bundle Capacity (mm)	50.8
Min. Bundle Diameter (In.)	3/16
Min. Bundle Diameter (mm)	4.8
Outside Diameter (In.)	0.25
Outside Diameter (mm)	6.4
Pricing Description	Spiral Wrap, .25" (6.3mm) x 1000', Flame Retardant Poly, White
Temperature Range	-4°F– 167°F (-20°C– 75°C)
Type	Spiral Wrap
Wall Thickness (In.)	0.040
Wall Thickness (mm)	1.02
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.