

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)

 **Text Search: 'TG70IG8'**

Your search criteria matched only one product, shown below

## TG70IG8



*Pan-Way*® TG-70 Surface Raceway is a two-piece multi-channel capable system to route, protect and conceal data, voice, video, fiber optic and power cabling.

- UL and CSA rated 600 V; meets UL 5A and CSA C22.2 No. 62.1-03 standards; FT4 rated
- Large cable capacity with aesthetically pleasing design
- Tamper resistant
- Compatible with 70mm faceplates or *Pan-Way*® Classic Series Snap-On Faceplates
- Transitions to *PANDUIT* T-45 and LD profile raceway
- Supplied with pre-punched mounting holes

***All AW (Arctic White) and two and three meter products are only available outside of North America as a standard item. Contact customer service for minimum order quantities, stock and other color availability.***

Part Number	TG70IG8
RoHS Compliancy Status	Compliant
Part Description	TG-70 raceway base in 8' and 10' lengths. Supplied with pre-punched mounting holes.
Product Type	Power Rated Raceway
Color	International Gray
CSA 22.2 No.6293	Yes
UL5A Listed	Yes
CE Compliant	Yes
CE Marking	Yes
Pricing Description	TG-70 Power Rated MultiChannel Raceway Base and Cover 8ft.
Product Length	8'
Product Size	70
Raceway Size	5.32" x 2.68" (135.0mm x 68.0mm)
Min. Order UOM	FT
Min. Order Qty.	32
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.