



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'TGSICAW'

Your search criteria matched only one product, shown below

TGSICAW



A full complement of fittings with a 40mm (1.6) minimum bend radius, compliant with TIA/EIA 568-A.

• TG-70 fittings are designed to exceed the TIA/EIA-568-B and 569-B required minimum bend radius for high performance copper and fiber optic cabling systems

All AW (Arctic White) and two and three meter products are only available outside of North America as a standard item. Contact customer service for minimum order quantities, stock and other color availability.

	Part Number	TGSICAW
	RoHS Compliancy Status	Compliant
	Part Description	Inside corner fitting - Non-adjustable. Used to join sections of TG raceway at inside corners.
	Product Type	Power Rated Fittings
	Color	Arctic White
	UL5A Listed	Yes
	CE Compliant	Yes
	CE Marking	Yes
	Pricing Description	TG-70 Inside Corner Fitting- Non Adjustable
	Product Size	70
	Min. Order UOM	PC
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.