






PART MARK AND
BATCH NUMBER HERE


ANGLE 1



ANGLE 2



ANGLE 3
LOW PROFILE OPTION



ANGLE 3


DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:				 Polamco	
J.CLARK		14/08/2011			60H SERIES					
DESIGN APPROVAL		DATE		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	TITLE:				 TE connectivity	
K.SHEPPARD		07/09/2011			MEMORY METAL RING ADAPTOR					
DOC TYPE	Customer Drawing			MATERIAL SEE PART NUMBER BREAKDOWN	ASSY USED ON: MIL-DTL-38999 SERIES III & IV		RESTRICTED TO:		 TE connectivity	
ISSUE/REV AA	DCR ---		FINISH SEE PART NUMBER BREAKDOWN		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP			
NCAGE CODE U5792		WEIGHT 32.25 g						SHT 1	DRAWING NO: P10745	

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØT MIN	C MAX	D MAX	E MAX	F MAX	K ±0,5	J MAX	F' MAX	MAX ENTRY FOR LOW PROFILE OPTION
09	M12 x 1.0	18,0	6,7	13,1	26,8	25,7	26,4	17,5	18,0	27,4	04
11	M15 x 1.0	21,0	10,2	13,9	27,6	26,7	28,2	17,5	22,0	29,2	05
13	M18 x 1.0	24,5	13,5	14,5	28,0	31,2	29,7	20,0	22,0	30,7	06
15	M22 x 1.0	29,0	16,2	15,5	29,0	37,2	31,2	24,5	25,0	32,2	07
17	M25 x 1.0	32,5	19,4	16,1	29,8	40,2	32,9	26,7	27,0	33,9	08
19	M28 x 1.0	35,5	21,8	16,8	30,6	44,7	34,5	27,0	28,0	35,7	10
21	M31 x 1.0	37,0	25,1	17,1	30,9	49,2	36,1	30,5	29,0	37,1	10
23	M34 x 1.0	40,0	28,2	17,7	31,2	51,7	37,6	31,5	31,7	38,6	10
25	M37 x 1.0	43,5	31,4	18,4	32,1	53,2	39,1	28,5	31,7	40,1	10

TABLE 2

ENTRY SIZE	ØG MIN	ØH MAX	ØM MAX
04	6,3	14,3	9,5
05	7,9	15,8	11,1
06	9,5	17,4	12,7
07	11,1	19,0	14,3
08	12,7	20,6	15,9
10	15,8	23,8	19,0
12	19,0	27,0	22,2
14	22,2	30,1	25,4
16	25,4	33,3	28,6
18	28,5	36,5	31,8
20	31,7	39,7	34,9
22	34,9	42,8	38,1
24	38,1	46,0	41,3

TABLE 3

CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS

60H1-17-08-1-C-A

SERIES _____

CONNECTOR INTERFACE _____

ANGLE _____

SHELL SIZE (TABLE 1) _____

ENTRY SIZE (TABLE 2) _____

MATERIAL _____

ALUMINIUM ALLOY

FINISH (TABLE 3) _____

LOW PROFILE OPTION (90° ONLY)


OMIT IF STANDARD REQUIRED

RING OPTION _____

A - RING TO SUIT SINGLE BRAID

B - RING TO SUIT DOUBLE BRAID

OMIT IF NO RING REQUIRED

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:					 Polamco 
J.CLARK		14/08/2011			60H SERIES					
DESIGN APPROVAL		DATE			TITLE:					
K.SHEPPARD		07/09/2011								
				UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	MEMORY METAL RING ADAPTOR					
Customer Drawing				MATERIAL						
DOC TYPE					SEE PART NUMBER BREAKDOWN	ASSY USED ON: MIL-DTL-38999 SERIES III & IV			RESTRICTED TO:	
ISSUE/REV AA		DCR ---			FINISH	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	
NCAGE CODE U5792			WEIGHT		SEE PART NUMBER BREAKDOWN				SHT 2	DRAWING NO: P10745