

AUTOMATION & CONTROL

HDMI 1.4 High Speed with Ethernet Male-to-Male Cables



- ▶ High Resolution 1080P and 3-D Ready
- ▶ Gold Plated HDMI Connectors
- ▶ CL3 Fire Rated for In-Wall Use
- ▶ Backward Compatible to 1.1, 1.2 and 1.3
- ▶ 75 Ft. and 100 Ft. Cables Have Built-In Repeaters

ENCLOSURES

RF Coaxial Cable Assemblies

BNC Male-to-BNC Male



50 Ohm — RG58A/U

Stock No.	Mfr.'s Type	Length	EACH
70121211	RFC-1111	12"	6.59
70121212	RFC-1112	24"	6.75
70121213	RFC-1113	36"	8.68
70121214	RFC-1114	5'	8.08
70121215	RFC-1115	7'	10.29
70121216	RFC-1116	10'	9.59

75 Ohm — RG59B/U

Stock No.	Mfr.'s Type	Length	EACH
70121217	RFC-1121	12"	6.35
70121218	RFC-1122	24"	6.75
70121219	RFC-1123	36"	7.42
70121220	RFC-1124	5'	8.80
70121221	RFC-1125	7'	8.80
70121222	RFC-1126	10'	9.59

POWER

BNC Male-to-BNC Right-Angle Male



50 Ohm — RG58A/U

Stock No.	Mfr.'s Type	Length	EACH
70121223	RFC-1211	12"	7.04
70121224	RFC-1212	24"	7.50
70121225	RFC-1213	36"	8.08
70121226	RFC-1214	5'	8.80
70121227	RFC-1215	7'	9.59
70121228	RFC-1216	10'	10.45

CABLE ASSEMBLIES

SMA Male-to-SMA Male



50 Ohm — RG58C/U

Stock No.	Mfr.'s Type	Length	EACH
70121247	RFC-1531	12"	6.17
70121248	RFC-1532	24"	6.50
70121249	RFC-1533	36"	7.16
70121250	RFC-1534	5'	7.79
70121251	RFC-1535	7'	8.52
70121252	RFC-1536	10'	10.83

75 Ohm — RG59B/U

Stock No.	Mfr.'s Type	Length	EACH
70121253	RFC-1521	12"	6.17
70121254	RFC-1522	24"	6.90
70121255	RFC-1523	36"	9.36
70121256	RFC-1524	5'	11.52
70121257	RFC-1525	7'	14.78
70121258	RFC-1526	10'	19.31

TEST & MEASUREMENTS

PASSIVE & ACTIVE

Fiber Optic Patch Cords

Quest Technology introduces quality patch cords at a low cost. These assemblies are ideal to meet your ST/PC and SC/PC cable requirements. All cables in this category are assembled using durable and reliable machine polished ceramic ferrules, not composite ferrules often used in low cost assemblies. Quest Technology fiber optic patch cords provide the highest quality and maximum performance expected from ceramic ferrule connectors. Individual test reports are available upon request. Custom lengths available on request. Call your Allied sales representative for details.

Duplex Single Mode



Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-49
70121397	NFO-STST-S9DX-1M	1 Meter ST/ST, DX, SM	11.74	11.34	10.62
70121398	NFO-SCST-S9DX-1M	1 Meter ST/SC, DX, SM	11.74	11.34	10.62
70121399	NFO-LCST-S9DX-1M	1 Meter LC/ST, DX, SM	14.37	13.88	13.00
70121400	NFO-SCSC-S9DX-1M	1 Meter SC/SC, DX, SM	11.74	11.34	10.62
70121401	NFO-LCSC-S9DX-1M	1 Meter LC/SC, DX, SM	14.37	13.88	13.00
70121402	NFO-LCLC-S9DX-1M	1 Meter LC/LC, DX, SM	14.69	14.19	13.29
70121403	NFO-STST-S9DX-3M	3 Meter ST/ST, DX, SM	13.03	12.59	11.79
70121404	NFO-SCST-S9DX-3M	3 Meter ST/SC, DX, SM	13.03	12.59	11.79
70121405	NFO-LCST-S9DX-3M	3 Meter LC/ST, DX, SM	15.66	15.13	14.17
70121406	NFO-SCSC-S9DX-3M	3 Meter SC/SC, DX, SM	16.64	15.13	13.87
70121407	NFO-LCSC-S9DX-3M	3 Meter LC/SC, DX, SM	15.66	15.13	14.17
70121408	NFO-LCLC-S9DX-2M	3 Meter LC/LC, DX, SM	15.25	14.73	13.79
70121409	NFO-STST-S9DX-5M	5 Meter ST/ST, DX, SM	14.28	13.80	12.92
70121410	NFO-SCST-S9DX-5M	5 Meter ST/SC, DX, SM	14.28	13.80	12.92
70121411	NFO-LCST-S9DX-5M	5 Meter LC/ST, DX, SM	16.91	16.34	15.30
70121412	NFO-SCSC-S9DX-5M	5 Meter SC/SC, DX, SM	14.28	13.80	12.92
70121413	NFO-LCSC-S9DX-5M	5 Meter LC/SC, DX, SM	16.91	16.34	15.30
70121414	NFO-LCLC-S9DX-5M	5 Meter LC/LC, DX, SM	17.23	16.65	15.59

Stock No.	Mfr.'s Type	Length	AWG	EACH
70121551	HDI-1403	3'	28	7.08
70121552	HDI-1406	6'	28	8.85
70121553	HDI-1410	10'	28	12.37
70121554	HDI-1412	12'	28	14.37
70121555	HDI-1415	15'	28	16.15
70121556	HDI-1420	20'	28	20.62
70121557	HDI-1425	25'	28	24.05
70121558	HDI-1430	30'	26	31.60
70121559	HDI-1450	50'	26	56.34
70277352	HDI-1475R	75'	26	104.17
70277353	HDI-1400R	100'	26	120.92

UHF Male-to-UHF Male



50 Ohm — RG58A/U

Stock No.	Mfr.'s Type	Length	EACH
70121278	RFC-2214	5'	10.53
70121279	RFC-2215	7'	11.46
70121280	RFC-2216	10'	14.60

TNC Male-to-TNC Male



50 Ohm — RG58A/U

Stock No.	Mfr.'s Type	Length	EACH
70121281	RFC-1411	12"	8.80
70121282	RFC-1412	24"	10.97
70121283	RFC-1413	36"	9.85
70121284	RFC-1414	5'	10.74
70121285	RFC-1415	7'	11.70
70121286	RFC-1416	10'	12.76

N Male-to-N Male



50 Ohm — RG58A/U

Stock No.	Mfr.'s Type	Length	EACH
70121260	RFC-1811	12"	9.78
70121261	RFC-1812	24"	10.19
70121262	RFC-1813	36"	12.67
70121263	RFC-1814	5'	11.80
70121264	RFC-1815	7'	9.77
70121265	RFC-1816	10'	14.01

50 Ohm — RG213/U

Stock No.	Mfr.'s Type	Length	EACH
70121266	RFC-1842	24"	18.14
70121267	RFC-1843	36"	16.75
70121268	RFC-1844	5'	20.20
70121269	RFC-1845	7'	30.87
70121270	RFC-1846	10'	26.93
—	—	—	—

OPTOELECTRONICS

ASSEMBLY

INDEX

Duplex Multi-Mode



Stock No.	Mfr.'s Type	Description	EACH		
			1-9	10-24	25-49
70121415	NFO-STST-M6DX-1M	1 Meter ST/ST, DX, MM	9.97	9.63	9.02
70121416	NFO-SCST-M6DX-1M	1 Meter ST/SC, DX, MM	9.97	9.63	9.02
70121417	NFO-LCST-M6DX-1M	1 Meter LC/ST, DX, MM	16.15	15.85	15.32
70121418	NFO-SCSC-M6DX-1M	1 Meter SC/SC, DX, MM	9.97	9.63	9.02
70121419	NFO-LCSC-M6DX-1M	1 Meter LC/SC, DX, MM	13.96	13.48	12.63
70121420	NFO-LCLC-M6DX-1M	1 Meter LC/LC, DX, MM	21.46	20.73	19.41
70121421	NFO-STST-M6DX-3M	3 Meter ST/ST, DX, MM	14.24	13.76	12.89
70121422	NFO-SCST-M6DX-3M	3 Meter ST/SC, DX, MM	15.84	11.19	10.48
70121423	NFO-LCST-M6DX-3M	3 Meter LC/ST, DX, MM	13.37	12.91	12.09
70121424	NFO-SCSC-M6DX-3M	3 Meter SC/SC, DX, MM	14.01	13.53	12.67
70121425	NFO-LCSC-M6DX-3M	3 Meter LC/SC, DX, MM	13.37	12.91	12.09
70121426	NFO-LCLC-M6DX-3M	3 Meter LC/LC, DX, MM	15.39	14.87	13.92
70121427	NFO-STST-M6DX-5M	5 Meter ST/ST, DX, MM	13.19	12.74	11.93
70121428	NFO-SCST-M6DX-5M	5 Meter ST/SC, DX, MM	13.19	12.74	11.93
70121429	NFO-LCST-M6DX-5M	5 Meter LC/ST, DX, MM	15.10	14.59	13.66
70121430	NFO-SCSC-M6DX-5M	5 Meter SC/SC, DX, MM	15.41	14.89	13.94
70121431	NFO-LCSC-M6DX-5M	5 Meter LC/SC, DX, MM	15.10	14.59	13.66
70121432	NFO-LCLC-M6DX-5M	5 Meter LC/LC, DX, MM	15.49	15.02	14.57