



RG-59U

- 1.REMARK:RG-59U CABLE
 INNER CONDUCTOR:0.643 CCS
 DIELECTRIC:PE-OD:3.7mm
 BRAID:32X0.12mm
 JACKET:BLACK PVC OD5.95mm
 2.RG-59U 500HM COAXIABLE CABLE



NBC-1706