




Flat



BLADE:	B
Drawing	
Mark	

REV	DATE	MODIFICATION	DRAWN
2013/09/05			

SPECIFICATIONS

1.ELECTRICAL:

UL APPLICATIONS: 250 VOLTS AC MAX., AT 2 AMPS.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 VOLTS AC.

INSULATION RESISTANCE: 100 M Ω .

TERMINATION: RESISTANCE 20m Ω MAX AFTER

ENVIRONMENTAL TESTING.

2. MECHANICAL:

CABLE-TO-PLUG TENSILE STRENGTH: 19.6N/PCS MIN

DURABILITY : 200 MATING CYCLES.

3.MATERIAL & FINISH:

HOUSING: POLYCARBONATE, UL94V-0 OR UL94V-2.

COLOR : TRANSPARENT OR OTHER COLOR ARE AVAILABLE.

CONTACT BLADE: COPPER ALLOY.

CONDUCTOR : SOLID WIRE , 24AWG, 26 AWG.

GOLD PLATING: 15u".

QUEST INTERNATIONAL, INC. 11200 NW 138th St. Medley, FL 33178		Quest Technology International, Inc. 11200 NW 138th St. Medley, FL 33178	
DIMENSION IN mm (Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED		材 质 MATERIAL	图 号 Dwg No.
.X±0.20		PC	NMP-4111
.XX±0.10		名称 TITLE	比例 SCALE
.X°±5°		MODULAR PLUG 6P4C FOR FLAT CABLE.	2 / 1
.XX°±2°		SOLD WIRE	张数 SHEET
审核 APPROVAL	核 对 CHECKED	制图 DRAWN	更改 REV
		Cathylli	重改 PROJ. A

1-

2-

ယ-

4-

61-

৯-

ST-DR-009A

-2-