




Round

SPECIFICATIONS
1. ELECTRICAL:
UL APPLICATIONS: 250 VOLTS AC MAX. AT 2 AMPS.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 VOLTS AC.
INSULATION RESISTANCE: 100 M Ω .
TERMINATION: RESISTANCE: 20m Ω MAX AFTER ENVIRONMENTAL TESTING.
2. MECHANICAL:
CABLE-TO-PLUG TENSILE STRENGTH : 19.6N/PCS MIN.
DURABILITY : 200 MATING CYCLES.
3. MATERIAL & FINISH:
HOUSING: POLYCARBONATE, UL94V-0 OR UL94V-2.
CONTACT BLADE: COPPER ALLOY.
CONDUCTOR : SOLID WIRE, 24AWG, 26 AWG.
GOLD PLATING: 50u".

BLADE:	B
Drawing	
Mark	

REV	DATE	MODIFICATION	DRAWN
2013/09/05			

Quest Technology International, Inc. 11200 NW 138th St. Medley, FL 33178			
DIMENSION IN mm (Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED		MATERIAL	图号 DWG NO.
.X $\pm$ 0.20		PC	NMP-6225
.XX $\pm$ 0.10		名称 TITLE	MODULAR PLUG 8P6C FOR ROUND CABLE.
审核 APPROVAL	核对 CHECKED	制图 DRAWN	比例 SCALE
		Cathylia	2/1
			张数 SHEET
			更改 REV
			A