


- Notes:
1. Material: Nylon 6.6
 2. Flammability Rating: UL94V-2
 3. Maximum Operating Temp. 185F (85C)
 4. Minimum Tensile Rating: 50 lbs.
 5. Maximum Bundle Diameter (Noted Below)
 6. UL 62275 Type 2/21
 7. Min. Installation Temp. -20C (-4F)

Material Designations: -9 = Natural -# = Color -0 = UV Black -HS= Heat Stabilized Black			Quest Technology Int'l, Inc. <small>112000 HWY 138TH ST., SUDBURY, ON, CANADA</small> <small>TEL: 905-513-9999 FAX: 905-513-9976</small> <small>www.questtechnology.com</small>		Standard Cable Tie 50 LB. Series	
	AEM No.	Maximum Bundle Dia.	A		+/- .030	
	B7S	1.875 (47.6)	7.562			
	B11S	3.0 (76.2)	11.125			
	B14S	4.0 (101.6)	14.562			
Unless Otherwise Specified All dimensions are in inches.	SIZE A	FSCM NO.	DWG NO. NWT-41XX		REV 2	
	SCALE N/A	Material Nylon 6/6		SHEET 1 of 1		