



NOTES:

1. MATERIAL: NYLON 6,6
2. FLAMMABILITY RATING:UL94V-2
3. MAXIMUM OPERATING TEMP: 185F (85C)
4. MINIMUM TENSILE RATING: 50 LB.
5. MAXIMUM BUNDLE DIA: NOTED BELOW
6. UL 62275 Type 221
7. MIN INSTALL TEMP. -20C (-4F)

MAXIMUM BUNDLE DIA.	A +/- .030
2.0 [50.8]	8.125 [206.4]
3.0 [76.2]	11.625 [295.3]
4.0 [101.6]	15.125 [384.2]

**** = PACKAGE**
M = 1,000 D = 500 H = 250
C = 100 L = 50 Q = 25

*** = NUMBER/COLOR**
0 - Black
9 - Natural

ALL DIMENSIONS ARE FOR REFERENCE ONLY
UNLESS OTHERWISE SPECIFIED ALL
DIMENSIONS ARE IN INCHES [MM]



Quest Technology Int'l, Inc.
11200 NW 159th St, Wesley, FL 32378
Tel: 305-513-8583 Fax: 305-513-9675
www.QuestTechnologyInt.com

Standard Mounting Head Cable Tie 50 LB Series

SIZE A	FSCM NO.	DWG NO. NWT-420X	REV 3
SCALE N/A	Material Nylon 6/6	SHEET 1 of 1	