

Surge Strips

- 4 to 8 AC outlets 120V / 15A
- 900 to 2800 joule surge protection
- Circuit breaker switch
- 4 ft. to 12 ft. power cord
- Response time of <1ns
- Indoor use
- EPD-1808 offers child protection
- ETL approved
- Lifetime Warranty



Fig. 1



Fig. 2



Fig. 3



Fig. 4

LIFETIME
WARRANTY



Item#	Figure	Color	AC Outlets	Cord Length	Outlet Position	Lit Power Switch	AC Power Adapter Ports	EMI/RFI	Surge Protected
EPD-1304	FIG. 1	WHITE	4	4 FT.	STRAIGHT	YES	0	NO	YES
EPD-1306	FIG. 2	WHITE	6	6 FT.	STRAIGHT	YES	0	NO	YES
EPD-1907	FIG. 3	YELLOW/BLACK	7	10 FT.	STRAIGHT	YES	1	NO	YES
EPD-1808	FIG. 4	WHITE	8	12 FT.	90 DEGREE	YES	3	YES	YES

Specifications

Item#	Wire AWG	AC Power	USB Charge Volts/Amps	Surge Protected	Joule Ratings	Clamping Voltage	Max Spike Current
EPD-1304	SJT 14AWG/3C	15A/125V/60HZ/1875W	N/A	YES	300	700V	15,000A
EPD-1306	SJT 14AWG/3C	15A/125V/60HZ/1875W	N/A	YES	300	700V	15,000A
EPD-1907	SJT 14AWG/3C	15A/125V/60HZ/1875W	N/A	YES	900	500V	45,000A
EPD-1808	SJT 14AWG/3C	15A/125V/60HZ/1875W	N/A	YES	2,800	500V	135,000A