





HDI-2303	HDI-2306	HDI-2312
L=3FT±30mm	L=6FT±30mm	L=12FT±50mm

[(1C/0.2TC+FPE ID:0.5)*1P+1C/0.2TC+PEOD:0.4+MYAL]*5P+
(1C/0.2TC+HDPE ID:0.45)*4C+AL+1/0.2BC+96#/0.12AL+PVC BLACK
OD:5.0 L=3FT±30mm /6FT±30mm/12FT±50mm

1. **Test Condition:**
 - (1) 100% OPEN & SHORT TEST;
 - (2) Insulation Resistance: DC300V 5MΩ(Min) ;
 - (3) Conductor Resistance: 5Ω/Max.
2. **The product is ROHS compliant.**
3. **HDTV-DVD TEST:1080P&3D&4K*2K**

PIN Assignment

P1	Color	P2	Color	Pairing
1	Brown	2	White	1Pair
3	Drain	3	Drain	
4	Blue	5	White	2Pair
6	Drain	6	Drain	
7	Green	8	White	3Pair
9	Drain	9	Drain	
10	Red	11	White	4Pair
12	Drain	12	Drain	
13	White	14	Orange	5Pair
15	Orange	15	Yellow	
16	Yellow	16	Red	
17	Drain	17	Drain	

Shell ——— Braid ——— Shell

 Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178 Tel: 305-513-8593 Fax: 305-513-9675 www.QuestTechnologyInt'l.com				DESCRIPTION	HDMI (M-M) W/ETHERNET 4K2K, 32AWG	SCALE	FIT	UNITS: MM	3RD ANGLE
				MODEL NO,	HDI-23xx				
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO,					
		ELLA	ELLA	FINISHING			2016/04/12	A1	
				MATERIAL		SYM	DATE	REVISION	