



**CONNECTORS**

**RECTANGULAR CONTACT INSERTS**



✓ Active

TE CONNECTIVITY (TE)

## MTC100-JA2-S14

Raychem | MT1000 , MTC

697121-000

TE Internal Number: 697121-000

Alias ID: 7-1195471-6

Not EU RoHS Compliant

Not EU ELV Compliant

**Contact Type** Socket

**Number of Positions** 20

**Connector & Contact Terminates To** Wire & Cable

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

**Wafer Assembly, Socket, A, Style, 2 Inch, 20 Contacts, With Oval Entry For 20-26 AWG. Temperature Rating 125 Deg. C MTC100 Series**

PDF

**English**

CAD Files

**Customer View Model**

3D\_STP.ZIP

**English**

**Customer View Model**

2D\_DXF.ZIP

**English**

## 3D PDF

PDF

3D

## Customer View Model

3D\_IGS.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Connector & Contact Terminates To** Wire & Cable

**Shell Size** 50.8 [2]

**Product Size** 2

**Product Type** Contact Insert

### Configuration Features

**Number of Positions** 20

**Keying** A

### Body Features

**Color** Black

**Insert Type** Environmental

**Insert Style** Socket

**Interfacial Seal** Without

**Module Material** High Grade Polyarylene Thermoplastic

**Rear Grommet** Without

### Contact Features

**Contact Type** Socket

### Dimensions

**Wire Range (AWG)** 20 – 26

### Operation/Application

**For Use With** Round Wire

### Packaging Features

**Packaging Quantity** 1

## PRODUCT COMPLIANCE



Statement of Compliance

## Statement of Compliance

PDF

---