



2-1194896-8 Product Details

[+ Share](#) [Print](#) [Email](#)


✓ Active

Shield Terminators

ST63-1-00

2-1194896-8 (ST63-1-00)

TE Internal Number: 619819-000

Product Highlights [View All](#)

- Shield Terminator
- Terminator Type = Solder Sleeve
- Fluid Resistance = Immersion
- Cable Temperature Rating = 125 °C
- Jacket Outer Diameter = 1.90 mm

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type Shield Terminator

Termination Features

Terminator Type Solder Sleeve

Dimensions

Shield O.D. (Min.) (mm [in]) 0.90 [0.035]

Length (Max.) (mm [in]) 16.50 [0.650]

Body Features

Jacket Outer Diameter (mm [in]) 1.90 [0.075]

Configuration Features

Preinstalled Lead Without

Temperature Indication System With

Temperature Indication System Type Fusible Ring

Industry Standards

Government/Industry Qualification No

RoHS/ELV Compliance Not ELV/RoHS compliant

Lead Free Solder Processes Not relevant for lead free process

MIL or NAS Specification (MIL-S-83519) (NAS 1747) NAS-1747

Environmental

Fluid Resistance Immersion

Operating Temperature (Max.) (°C) 150

Conditions for Usage

Cable Temperature Rating (°C) 125

Other

Brand Raychem

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

