



44A1121-22-9/9-9 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A1121-22-9/9-9

44A1121-22-9/9-9 ✔

TE Internal Number: 382002-000

Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United Kingdom
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Cable Type [?]	Spec 44
Cable Style [?]	Jacketed, Round-Braid Shielded

Electrical Characteristics

Voltage Rating (VAC)	600
----------------------	-----

Dimensions

Conductor Outer Diameter (mm [in])	0.79 [0.031]
Shield (Screen) Diameter (mm [in])	2.95 [0.116]

Body Features

Wire Size (AWG/CM)	22 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	White
Nominal Outside Diameter (mm [in])	3.35 [0.132]
Wire Diameter (mm [in])	1.19 [0.0468]

Configuration Features

Number of Conductors	Twisted Pair
----------------------	--------------

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	-65 - +150
Wire Size - Details	22 AWG 0.38 mm ² , 0.00059 in ² , 19 x 34 AWG

Operation/Application

Application	General Purpose - Light Weight
-------------	--------------------------------

Packaging Features

Wire Source	United Kingdom
-------------	----------------

Other

Brand	Raychem
Node Classification	Twisted Pair Cable

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

