



44A1121-20-9/96-9 Product Details

[Share](#) | [Print](#) | [Email](#)


✓ Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A1121-20-9/96-9

44A1121-20-9/96-9

TE Internal Number: 3833393001

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United Kingdom
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 20 AWG
- Voltage Rating = 600 VAC

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Cable Type	Spec 44
Cable Style	Jacketed, Round-Braid Shielded

Electrical Characteristics	
Voltage Rating (VAC)	600

Dimensions	
Conductor Outer Diameter (mm [in])	1.02 [0.040]
Shield (Screen) Diameter (mm [in])	3.35 [0.132]

Body Features	
Wire Size (AWG/CM)	20 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	White, White w/ Blue Stripe
Nominal Outside Diameter (mm [in])	3.76 [0.148]
Wire Diameter (mm [in])	1.40 [0.055]

Configuration Features	
Number of Conductors	Twisted Pair

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	-65 - +150
Wire Size - Details	20 AWG 0.62 mm ² , 0.00095 in ² , 19 x 32 AWG

Operation/Application

Application	General Purpose - Light Weight
-------------	--------------------------------

Packaging Features

Wire Source	United Kingdom
-------------	----------------

Other

Brand	Raychem
Node Classification	Twisted Pair Cable

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

