



Search by part # or keyword

Products

Industries & Solutions

Resources

TE Store

Sign In



Wire And Cable > Hook Up Wire

44AM1111-24-9-9

44AM1111-24-9-9



X

After your visit, would you be willing to provide some quick feedback?

(It will only take a minute)

Yes


No Thanks

1111-24-9-9

Radiation Cross-

ed Copper

Compatible Parts & Tooling



We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Feedback

Documents	Features	Product Compliance
Product Drawings	Dimensional Drawing 44AM1111-24-9-9 44AM1111-24-9-9 English	
Datasheets & Catalog Pages	1654025_Sec9_SPEC44 ENG_CS_1654025_Sec9_SPEC44_0313.pdf English	
Product Specifications	Product Specification ENG_SS_SPEC44_5.pdf English	
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Cable Type : Spec 44	
Electrical Characteristics	Voltage Rating (V): 600	
Body Features	Insulation Material : Modified Radiation Cross-linked PVDF Conductor Material : Tin-Coated Copper	



hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Products with Similar Specs

[View All Similar Products](#)


THIS PRODUCT

TOP RESULTS ?

HOOK UP WIRE

44AM1111-24-9-9

44AM1111-24-9-9




In-Stock

Cable Type : **Spec 44**
 Voltage Rating : **600 V**
 Insulation Material : **Modified Radiation Cross-linked PVDF**
 Conductor Material : **Tin-Coated Copper**
 Wire Size : **24 AWG**

HOOK UP WIRE

44AM1111-24-9-9CS2275

44AM1111-24-9-9CS2275




From **In-Stock**

Cable Type : **MIL-DTL-27500**
 Voltage Rating : **600 V**
 Insulation Material : **Modified Radiation Cross-linked PVDF**
 Conductor Material : **Tin-Coated Copper**
 Wire Size : **24 AWG**

HOOK UP WIRE

44A1111-24-9-9-MX

44A1111-24-9-9



Non-Stocked

Cable Type : **Spec 44**
 Voltage Rating : **600 V**
 Insulation Material : **Modified Radiation Cross-linked PVDF**
 Conductor Material : **Tin-Coated Copper**
 Wire Size : **24 AWG**

HOOK UP WIRE

44AM1111-24-6-9CS2275B

44AM1111-24-6-9CS2275B



In-Stock

Cable Type : **MIL-DTL-27500**
 Voltage Rating : **600 V**
 Insulation Material : **Modified Radiation Cross-linked PVDF**
 Conductor Material : **Tin-Coated Copper**
 Wire Size : **24 AWG**

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)