



Search by part # or keyword

Products

Industries & Solutions

Resources

TE Store


Sign In



Wire And Cable Products > Hook Up Wire

81044/12-24-94

81044/12-24-94



Raychem

TE Internal #: **282642-000**

TE Internal Description: **81044/12-24-94**

Mil-Spec: **M81044/12-24-94**

Alias #: **2-1192121-3**

Cable Type : **MIL-DTL-81044**

Voltage Rating (V): **600**


Insulation Material : **Modified Radiation Cross-linked PVDF**

Conductor Material : **Tin-Coated Copper**

Wire Size (AWG): **24**

[Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling



We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Documents	Features	Product Compliance
Product Drawings	<p>WIRE, ELECTRIC, RADIATION-CROSSLINKED, TIN-COATED COPPER, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT</p> <p>tif English</p> <p>81044/12-24-94</p> <p> 81044/12-24-94 English</p>	
Datasheets & Catalog Pages	<p>1654025_Sec9_SPEC44</p> <p> ENG_CS_1654025_Sec9_SPEC44_0313.pdf</p> <p>English</p>	
Product Specifications	<p>Product Specification</p> <p> ENG_SS_SPEC44_5.pdf English</p>	
<p>Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.</p>		
Product Type Features	<p>Cable Type : MIL-DTL-81044</p> <p>Product Classification :</p> <p>Cable - High Performance - Spec 44, 55 & RCW</p> <p>Product Type : Cable</p> <p>Cable Style : Primary</p>	



Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?


HOOK UP WIRE
81044/12-24-94
81044/12-24-94



Non-Stocked

Cable Type : **MIL-DTL-81044**
Voltage Rating : **600 V**
Insulation Material : **Modified Radiation Cross-linked PVDF**
Conductor Material : **Tin-Coated Copper**


HOOK UP WIRE
81044/12-24-7
81044/12-24-7



In-Stock

Cable Type : **MIL-DTL-81044**
Voltage Rating : **600 V**
Insulation Material : **Modified Radiation Cross-linked PVDF**
Conductor Material : **Tin-Coated Copper**


HOOK UP WIRE
81044/12-24-0
81044/12-24-0



In-Stock

Cable Type : **MIL-DTL-81044**
Voltage Rating : **600 V**
Insulation Material : **Modified Radiation Cross-linked PVDF**
Conductor Material : **Tin-Coated Copper**

HOOK UP WIRE
81044/12-24-5
81044/12-24-5



Non-Stocked

Cable Type : **MIL-DTL-81044**
Voltage Rating : **600 V**
Insulation Material : **Modified Radiation Cross-linked PVDF**
Conductor Material : **Tin-Coated Copper**

Wire Size : **24 AWG**

Wire Size : **24 AWG**

Wire Size : **24 AWG**

Wire Size : **24 AWG**

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)