



B-015-22 Product Details

[+ Share](#) | [Print](#) | [Email](#)


✓ Active

Solder Sleeve Wire Splices

B-015-22

B-015-22

TE Internal Number: 696227-000

Product Highlights [View All](#)

- Coaxial Terminator
- Splice Type = Solder Sleeve
- Fluid Resistance = Splash Protection
- Wire Temperature Rating Range (Max.) = 85°C
- Inside Diameter = 9.00 mm

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Documents](#) | [Features](#) | [Compliance](#)

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Coaxial Terminator
Splice Type	Solder Sleeve

Termination Features

Connection Type	Solder
-----------------	--------

Dimensions

Inside Diameter (mm [in])	9.00 [0.355]
Inside Diameter Fully Recovered (mm [in])	3.80 [0.150]
Length (mm [in])	41.20 [1.622]

Industry Standards

RoHS/ELV Compliance 	Not ELV/RoHS compliant
Lead Free Solder Processes 	Not relevant for lead free process

Environmental

Fluid Resistance	Splash Protection
Operating Temperature (Max.) (°C)	125

Conditions for Usage

Wire Temperature Rating Range (Max.)	85°C
--------------------------------------	------

Operation/Application

Application	Coaxial Cable Termination
-------------	---------------------------

Other

Brand	Raychem
Node Classification	Coax Cable Termination

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

