



# DWTC-16/4-X-STK Product Details

[Share](#) | [Print](#) | [Email](#)

DWTC-16/4-X-STK Heat Shrink Tubing TE Connectivity

## Heat Shrink Tubing

DWTC-16/4-X-STK

**DWTC-16/4-X-STK**

TE Internal Number: 9998552005

✓ Active

### Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = DWTC
- Product Source = Czech Republic
- Semiflexible
- Medium Wall Style

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#)

**[Features](#)**

[Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

### Product Type Features

Product Type <sup>?</sup>	Heat Shrinkable Tubing
Color	Clear

### Dimensions

Expanded ID, Min. (mm [in]) <sup>?</sup>	16.00 [0.630]
Recovered ID, Max. (mm [in]) <sup>?</sup>	4.00 [0.157]
Cut Length (mm [in]) <sup>?</sup>	1220.00 [48.031]

### Body Features

Product Name	DWTC
Pliancy	Semiflexible
Wall Style <sup>?</sup>	Medium
Wall Type <sup>?</sup>	Dual
Lining Type <sup>?</sup>	Adhesive
Material	Irradated Modified Polyolefin
Shrink Ratio <sup>?</sup>	4:1
Fluid Type	Brake Fluid, Unleaded Gasoline
Resistant To	Fluids, Impact, Mechanical Damage
Wall Thickness - Full Recovery (Nominal) (mm [in])	1.50 [0.059]

### Housing Features

Material Systems	No
------------------	----

### Industry Standards

Government/Industry Qualification	No
Flammability Rating	Non-Flame-Retardant
Approved Standards	RK-6204
RoHS/ELV Compliance <sup>?</sup>	RoHS compliant, ELV compliant
Lead Free Solder Processes <sup>?</sup>	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

### Environmental

Fluid Resistance	Immersion
Operating Temperature (°C) <sup>?</sup>	-55 - +75

### Conditions for Usage

Full Recovery Temperature (°C)	100
Shrink Temperature, Min. (°C)	60
High Temperature Compatible	No

### Operation/Application

Emission Free Type	Halogen-free
Product Use	Brake Pipe Protection
Application	Automotive

### Packaging Features

Packaging Method	Stick
------------------	-------

### Product Availability

Product Source	Czech Republic
----------------	----------------

### Other

Brand	Raychem
-------	---------

### Related Products

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

