



## HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)

### X2-1.5-0-SP

Raychem | SWFR X2

X2-1.5-0-SP

TE Internal Number: EJ1478-000

Alias ID: 8-1899838-6

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Abrasion

Low Outgassing No

Product Source US

Packaging Method Spool



**PRODUCT DRAWING**

English

## DOCUMENTATION

Product Drawings

**SWFR X2 SINGLE WALL HEAT SHRINKABLE TUBING**

PDF

English

Catalog Pages/Data Sheets

**At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8**

PDF

English

**Highly Flame-Retardant, Zero Halogen, Low Recovery Temperature, Metric-Sized Heat-Shrinkable Tubing**

PDF

English

**1-1773894-4\_SWFR\_Tubing**

PDF

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Wall Type** Single

**Product Family** X2

---

### Electrical Characteristics

**Voltage (Max) (kV)** .6

---

### Body Features

**Shrink Ratio** 2:1

**Color** Black

**Flexibility** Very Flexible

**Material** ZEROHAL Polyolefin

**Fluid Type** Water

---

### Dimensions

**Recovered Wall Thickness (Nominal)** .44 mm [ .017 in ]

**Expanded Inside Diameter (Min)** 2.1 mm [ .083 in ]

**Recovered Inside Diameter (Max)** .75 mm [ .03 in ]

---

### Usage Conditions

**Resistant To** Abrasion

**Recovery Temperature (°C)** 90

**Operating Temperature Range (°C)** -55 – 105

**Flammability** Flame-Retardant

**Shrink Temperature (Min) (°C)** 70

**Fluid Resistance** Moisture/Spray Protection

---

### Product Availability

**Applicable Region** Global

---

### Packaging Features

**Packaging Method** Spool

---

### Other

**Low Outgassing** No

**Product Source** US

---

### Statement of Compliance

