



TE CONNECTIVITY (TE) - [Raychem](#)

81044/9-20-4

✓ **ACTIVE**

81044/9-20-4

TE Internal Number: 265716-000

Mil-Spec: M81044/9-20-4

Alias ID: 5-1191961-7

[Get a Sample](#)

[Compatible Parts & Tooling](#)

[Add to List](#) ▼ ▼ | [Documents](#) | [Features](#) | [Compliance](#) | [Similar Products](#)

↓ **PRODUCT DRAWING**
English

> [See All Documentation](#)

North America ▼

DISTRIBUTOR	PHONE	STOCK	DATE AS OF	
MASTER ELECTRONICS CORP.	1-888-473-5297	3,750	2018/01/07	Visit Site

[View More Distributors \(1\)](#)

DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

Product Drawings

WIRE, ELECTRIC, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, TIN-COATED COPPER, MEDIUM WEIGHT, AIRFRAME, 600 VOLT

PDF **(TIFF AVAILABLE)**

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Polyalkene-Insulated, Copper Or Copper Alloy

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Electrical Characteristics	Voltage Rating (V)	600
Dimensions	Wire Size (AWG)	20
	Wire Size (mm ²)	.52
Usage Conditions	Operating Temperature Range (°C)	-65 – 150
Statement of Compliance	Statement of Compliance PDF	

Compatible Products

[> Contact Product Support](#)

About TE Connectivity	For Partners	Customer Support	CALL US	LIVE CHAT	United States
<ul style="list-style-type: none"> Our Company Events TE News Center Careers Investors Corporate Responsibility Terms and Conditions of Sale 	<ul style="list-style-type: none"> Distributors Suppliers 	<ul style="list-style-type: none"> Email or Call Us Find Authorized Distributors What's New on TE.com Product FAQs 	<ul style="list-style-type: none"> Select Country & Language United States (EN) Germany (DE) China (中文) Japan (日本語) Afghanistan (EN) ▼ Find Your Country ▼ 		