




**HARNESSING**

**CABLE BRAIDS**



✓ Active

**TE CONNECTIVITY (TE)**

**LWB-103-10.0(50)**

LWB-103-10.0(50)

TE Internal Number: EG3247-000

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

**Product Type** Braid

**Plating** Nickel

**Braid Material** Copper Alloy

**Braid Coverage (%)** 90

[↓ PRODUCT DRAWING](#)  
English

## DOCUMENTATION

Product Drawings

**INSTALITE LIGHTWEIGHT SCREENING BRAID**

PDF

**English**

## FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

**Product Type** Braid

Electrical Characteristics

**DC Resistance (Nominal) (mΩ)** 9

---

Body Features

**Plating** Nickel

**Braid Material** Copper Alloy

---

Dimensions

**Cable Entry Diameter** 8 – 15 mm [ .315 – .591 in ]

**Length (ft)** 164.04

**Length (m)** 50

**Weight (Nominal) (kg/km)** 28

---

Usage Conditions

**Operating Temperature Range (°C)** -65 – 200

---

Packaging Features

**Packaging Quantity** 50

**Packaging Method** Reel

---

Other

**Braid Coverage (%)** 90

Statement of Compliance

**Statement of Compliance**

PDF

---