



CLASS	MATERIAL/FINISH
F	ALUMINIUM/NICKEL PLATED
K	STAINLESS STEEL/PASSIVATED
KE	STAINLESS STEEL/PASSIVATED
W	ALUMINIUM/OLIVE DRAB CADMIUM PLATED
Z	ALUMINIUM/ZINC NICKEL PLATED

CABLE ENTRY SIZE CODE	AA +/-0,1	BB +/-0,1	CC +/-0,3	DD +0,2/-0
A	4,7	7,7	12,2	1,12
B	6,4	9,4	14,0	1,12
C	7,9	11,0	15,5	1,12
D	9,5	12,6	17,1	1,12
E	11,1	14,1	18,7	1,12
F	12,7	15,7	20,3	1,12
G	15,9	18,9	23,5	1,12
H	19,1	22,0	26,7	1,12
J	22,2	25,2	29,8	1,75
K	25,5	28,4	33,0	1,75
L	28,6	31,5	36,2	1,75
M	31,8	34,7	39,4	1,75

SHELL SIZE	A MAX	B MAX	C THREAD	D +0/-0,25	D2 +0/-0,25	E MAX	G MAX	H MAX	J MAX	I MIN	N	MAXIMUM ENTRY SIZE
08	22,48	15,67	1/2-20 UNF	6,86	6,68 see note 3	15,30	16,10	10,20	31,05	4,95	12	B
10	25,65	18,64	5/8-24 UNEF	9,53	9,35 see note 3	15,30	17,90	13,70	34,21	4,95	15	D
12	28,83	21,79	3/4-20 UNEF	12,98	12,62 see note 3	15,30	19,40	16,80	37,95	4,95	21	F
14	32,00	24,99	7/8-20 UNEF	14,86	14,86	15,30	20,00	17,90	39,65	4,95	24	G
16	35,18	28,24	1-20 UNEF	18,03	17,73 see note 3	15,30	21,60	21,20	41,25	4,95	30	H
18	38,55	30,94	1 1/16-18 UNEF	20,04	20,04	15,30	22,60	23,20	43,75	4,95	33	H
20	41,53	34,16	1 3/16-18 UNEF	23,22	23,22	15,30	24,10	26,20	46,91	4,95	36	J
22	44,70	37,29	1 5/16-18 UNEF	26,39	26,39	15,30	25,70	29,40	50,10	4,95	39	K
24	47,89	40,46	1 7/16-18 UNEF	29,31	29,31	15,30	27,40	32,60	53,29	4,95	42	L
28	54,23	49,45	1 3/4-18 UNS	35,28	35,28	15,30	30,90	39,60	56,46	4,95	54	M

1 - MINIMUM PENETRATION OF ØD OR ØD2 FROM FRONT OF SERRATIONS
2 - PLEASE NOTE THERE MAY BE CROSSOVER DEPENDENT ON DIAMETER AND PITCH
3 - APPLY TOLERANCE +0,18/-0

SERIES _____

CLASS, MATERIAL FINISH (TABLE 1) _____

SHELL SIZE (TABLE 2) _____

CABLE ENTRY SIZE CODE (TABLE 4) _____

DRAWN	W.RUST	DATE 04/04/2014	 3RD ANGLE PROJECTION NOT TO SCALE	 POLAMCO LTD www.polamco.com	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	
SALES APPR	H.TAILLANDIER	04/04/2014					
DESIGN APPR	M. PAUL	04/04/2014	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 3°	ASSY USED ON: EN2997			
PROD APPR	J.STEPHENSON	04/04/2014		TITLE: 90 ° ANTI-DECOUPLING BANDING ADAPTOR			
QUAL APPR	P.REES	04/04/2014	MATERIAL SEE ABOVE FINISH SEE ABOVE	PART NUMBER: EN3660-065****		DRAWING NO: P20030	SHT 1
ISSUE 1	DCR ---						
NCAGE CODE U5792		WEIGHT					