





TO PRESS-FIT IN A .312±.003
(7.9±0.08) DIA. HOLE
IN A .25 (6.4) MIN.
THICK PANEL



PART NO.	"A" REF.	"B" REF.
WSBH-1-01	.51 (13.0)	.23 (5.8)
WSBH-2-01	.72 (18.3)	.44 (11.2)
WSBH-3-01	1.07 (27.2)	.79 (20.1)
WSBH-4-01	1.40 (35.6)	1.11 (28.2)

NOTES:

1. MATERIAL: NYLON 66 (RMS-01)
FLAME RETARDANT, NYLON (RMS-19).
BY SPECIAL ORDER.
2. COLOR: NATURAL.
COLOR: BLACK AVAILABLE BY SPECIAL ORDER.

			TITLE: WIRE SADDLE, BLIND HOLE				 	
D	SEE CO 200244 FOR CHANGES	SK 09.18.08	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # WSBH	DWN: P.B	DT: 09-14-94	FINAL	
C	SEE ECN #603 FOR CHANGES	SM 03.21.03		MAT'L: SEE NOTES	CHKD:	ENG:	PART #	PRINT TYPE CA
B	CHANGED FILE NUMBER	SM 05.30.01		RE: RICHCO, INC.	RICHCO INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE	
A	MAT'L RMS-19 ADDED	J.L. 12.29.97						
REV	DESCRIPTION	ENGR DATE						