



**Strain Relief - Cable Type: .250 in;.255 in;.290 in; Compatible Cable Shape: Round**

● In Stock !

Item Code: BSR005A

Heat Stabilized Nylon 6/6 Strain Relief Bushing installs into .500 in (12.7 mm) diameter openings to protect .250 in;.255 in;.290 in Round cables by absorbing the forces of push, pull, and twisting.



Description	Quantity	Options
Compatible Cable Shape	: Round	<input type="text" value="1000"/>
Cable Type	: .250 in;.255 in;.290 in	<a href="#">Add to Cart</a>
Compatible Hole Diameter	: .500 in (12.7 mm)	<a href="#">Free Sample</a>
Compatible Hole Width	: .450 in (11.4 mm)	<a href="#">Request Quote</a>
Color	: Black	
Full Material	: Heat Stabilized Nylon 6/6	
Type	: SV;HPD	
Compatible Hole Shape	: Round;Antirotational	
Wire Gauge	: 18/2;18/2;16/2	
Material Flammability Standard	: UL94 V-2	



Print Page

Products you might be interested in



Strain Relief - Cable Type: .250 in;.255 in;.290 in; Compatible Cable Shape: Round

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding  
Access Hardware  
Adhesives, Sealants & Tapes  
Bearings & Power Transmissions  
Caps & Plugs

Clamps & Workholdings  
Cutting & Machining  
Extrusions & Structural Systems  
Fasteners  
Feet, Casters & Glides

Fiber, Wire & Cable Management  
Flange Protection  
Knobs, Handles & Grips  
Material Handling  
Shop Supplies

PCB & Electronics Hardware  
Pneumatics & Hydraulics  
Raw Materials  
Tamper Evident & Security Seals  
Tooling & Positioning Components  
Tools & Precision Instruments

**About Us**

- [About Essentra Components](#)
- [About Essentra PLC](#)
- [Locations](#)

**Customer Service**

- [Contact Us](#)
- [Catalogs](#)
- [Sample Program](#)
- [Free CAD](#)
- [Careers](#)
- [Distributor Portal](#)

**Policies**

- [Privacy Policy](#)
- [Terms and Conditions of Sale](#)
- [Terms and Conditions of](#)
- [Purchase](#)
- [Environmental Policy](#)
- [Health and Safety](#)
- [Quality Statement](#)

**Terms of Use**

- [Website Terms of Use](#)
- [Cookie Policy](#)



**ABOUT SSL CERTIFICATES**