



## NSB3C-20/4

Type C, length 3, 20 IN (female/send) and 4 OUT (male/return)  
 Width: 87 mm, height: 77 mm, length: 372 mm

Supplied as disassembled set comprising of all hardware parts including plates, profiles, strain relief, end pieces and screws.



### Technical Information [hide](#)

<b>Product</b>	
Title	NSB3C-20/4
<b>Electrical</b>	
Contact resistance	< 5 mΩ (inner)
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current per contact	2 A
<b>Mechanical</b>	
Cable O.D.	15 - 20 mm multicore
Insertion force	≤ 10 N
Withdrawal force	≥ 10 N
Lifetime	> 1000 mating cycles
Wiresize	0.22 and 0.14 mm <sup>2</sup>
Wiresize	24 and 26 AWG
<b>Material</b>	
Shell	Aluminium
Quad plates	POM
End pieces	Thermoplastic
<b>Environmental</b>	
Temperature range	-25 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

**REAN**<sup>®</sup>  
REAN a brand of Neutrik AG