



NSB2B-16/0

Type B, length 2, 16 IN (female/send)
Width: 117 mm, height: 79 mm, length: 252 mm

Supplied as disassembled set comprising of all hardware parts including plates, profiles, strain relief, end pieces and screws.



Technical Information [hide](#)

Product	
Title	NSB2B-16/0
Electrical	
Contact resistance	< 5 mΩ (inner)
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current per contact	2 A
Mechanical	
Cable O.D.	15 - 20 mm multicore
Insertion force	≤ 10 N
Withdrawal force	≥ 10 N
Lifetime	> 1000 mating cycles
Wiresize	0.22 and 0.14 mm ²
Wiresize	24 and 26 AWG
Material	
Shell	Aluminium
Quad plates	POM
End pieces	Thermoplastic
Environmental	
Temperature range	-25 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN[®]
REAN a brand of Neutrik AG