



NYS225L

2 pole 1/4" plug, large shell for speaker cable, large cable outlet (9 mm)



Technical Information [hide](#)

Product	
Title	NYS225L
Connection Type	Plug
Gender	male
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Contact resistance	depends on mating connector
Rated current	depends on mating connector
Mechanical	
Cable O.D.	≤ 9 mm
Lifetime	1000 mating cycles
Wiresize	12 mm ²
Material	
Contact plating	2 μm Ni
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	SnCe plated, crimp type
Bushing	PVC

Insulation

Thermoplastic

Environmental

Solderability

Complies with IEC 68-2-20

Temperature range

-20 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN[®]
REAN a brand of Neutrik AG