



 Deutsche Version

[Home](#)

[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

☐ PRODUCTS ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NEUTRIK



Audio

3.5 mm Plugs

[back](#)

NYS226G

Product

Connector Type	Plug
Gender	male

Electrical

Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A

Mechanical

Cable O.D.	≤ 4 mm
Lifetime	5000 mating cycles

Material

Contact plating	0.2 µm Au
Contacts	Brass (CuZn39Pb3)
Insert	PA 66 30 % GR
Shell	Brass (CuZn39Pb3), gal Ni plated
Strain relief	CRIMP type snce plated

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C